	Service Bulletin	Issue by After Sales
	Matching new LCAC range 2017 versus old LCAC range 2014/2016	20/11/2017
		Rev : 3 SB10ARS
		Page 1 to 4

Object :

For 2017, we are introducing a new LCAC range benefiting of new communication bus with **2 wires** only* not polarised S1/S2

*except size 12



ID produit	Description produit
7SP032165	AWSI-DID012-N11
7SP032166	AWSI-DID018-N11
7SP032167	AWSI-DID024-N11
7SP032168	AWSI-DID036-N11
7SP032169	AWSI-DID048-N11
7SP032170	AWSI-DID060-N11



ID produit	Description produit
7SP042247	AWSI-CCD012-N11
7SP042248	AWSI-CCD018-N11
7SP042249	AWSI-CCD024-N11
7SP042250	AWSI-CCD036-N11
7SP042251	AWSI-CCD048-N11
7SP042258	AWSI-CCD030-N11




ID produit	Description produit
7SP012231	AWSI-FCD018-N11
7SP012232	AWSI-FCD024-N11
7SP012233	AWSI-FCD036-N11
7SP012234	AWSI-FCD048-N11
7SP012235	AWSI-FCD060-N11



ID produit	Description produit
7SP071407	AWSI-XBD012-N11
7SP071408	AWSI-XBD018-N11

ID produit	Description produit
7SP062891	AWAU-YMD012-H11
7SP062892	AWAU-YMD018-H11
7SP062893	AWAU-YMD024-H11
7SP062894	AWAU-YMD030-H11
7SP062895	AWAU-YMD036-H11
7SP062896	AWAU-YMD036-H13
7SP062897	AWAU-YMD042-H11
7SP062898	AWAU-YMD048-H11
7SP062899	AWAU-YMD048-H13
7SP062900	AWAU-YMD060-H13



	Service Bulletin	Issue by After Sales
	Matching new LCAC range 2017 versus old LCAC range 2014/2016	20/11/2017
		Rev : 3 SB10ARS
		Page 2 to 4

Customers may have in their stock old indoor units such ducted DCD, cassette CBD, ceiling FBD, console XAD or old outdoor unit YLD range.

This previous LCAC range was using 3 wires P/Q/E as communication bus (except size 12) for indoor and outdoor units.



ID produit	Description produit
7SP032158	AWSI-DCD012-N11
7SP032159	AWSI-DCD018-N11
7SP032142	AWSI-DCD024-N11
7SP032143	AWSI-DCD030-N11
7SP032144	AWSI-DCD036-N11
7SP032145	AWSI-DCD048-N11
7SP032146	AWSI-DCD060-N11



ID produit	Description produit
7SP042234	AWSI-CBD012-N11
7SP042243	AWSI-CBD012-N11
7SP042240	AWSI-CBD018-N11
7SP042244	AWSI-CBD018-N11
7SP042224	AWSI-CBD024-N11
7SP042225	AWSI-CBD030-N11
7SP042226	AWSI-CBD036-N11
7SP042227	AWSI-CBD048-N11
7SP042228	AWSI-CBD060-N11




ID produit	Description produit
7SP012225	AWSI-FBD018-N11
7SP022998	AWSI-FBD024-N11
7SP022999	AWSI-FBD030-N11
7SP023000	AWSI-FBD036-N11
7SP023001	AWSI-FBD048-N11
7SP023002	AWSI-FBD060-N11



ID produit	Description produit
7SP071403	AWSI-XAD012-N11
7SP071404	AWSI-XAD018-N11

ID produit	Description produit
7SP062821	AWAU-YLD012-H11
7SP062822	AWAU-YLD018-H11
7SP062823	AWAU-YLD024-H11
7SP062824	AWAU-YLD030-H11
7SP062825	AWAU-YLD036-H11
7SP062826	AWAU-YLD036-H13
7SP062827	AWAU-YLD048-H13
7SP062899	AWAU-YMD048-H13
7SP062828	AWAU-YLD060-H13
7SP062900	AWAU-YMD060-H13



	Service Bulletin	Issue by After Sales
	Matching new LCAC range 2017 versus old LCAC range 2014/2016	20/11/2017
		Rev : 3 SB10ARS Page 3 to 4

The question is the matching between **old** indoor units versus new outdoor units YMD **and** new indoor units versus **old** outdoor units YLD.


3 differents cases :


Case n°1 : Matching with old outdoor units YLD012 and new indoor unit size 12 **or** new outdoor units YMD012 versus old indoor units size 12 → does not work due to different communication protocol

Case n°2 : Matching with **new** outdoor units YMD and **old** indoor units LCAC range 2014 till 2016



Wiring



	Service Bulletin	Issue by After Sales
	Matching new LCAC range 2017 versus old LCAC range 2014/2016	20/11/2017
		Rev : 3 SB10ARS Page 4 to 4

Case n°3 : Matching with **old** outdoor units YLD and **new** indoor units LCAC range 2017



Important note :

FWDB range is only compatible with their own outdoor unit YMDB

Code produit	Description produit	Code produit2	Description produit2
7SP012246	AWSI-FWDB018-N11	7SP062924	AWAU-YMDB018-H11
7SP012247	AWSI-FWDB024-N11	7SP062925	AWAU-YMDB024-H11